

# Clevis foot LSNG-32

Part number: 31740

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Size	32
Based on norm	VDMA 24562
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-40 °C ... 150 °C
Max. load capacity	0.9 kN
Product weight	172 g
Note on materials	RoHS-compliant
Mounting material	High-alloy steel
Rod end bearing material	Steel PTFE