

Clevis foot LSNG-40

Part number: 31741

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	40
Based on norm	VDMA 24562
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-40 °C ... 150 °C
Max. load capacity	1.5 kN
Product weight	228 g
Note on materials	RoHS-compliant
Mounting material	High-alloy steel
Rod end bearing material	Steel PTFE