

# Clevis foot LSNG-100

Part number: 31745

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Size	100
Based on norm	VDMA 24562
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-40 °C ... 150 °C
Max. load capacity	9 kN
Product weight	1343 g
Note on materials	RoHS-compliant
Mounting material	Spherulitic graphite iron
Rod end bearing material	Steel PTFE