

Clevis foot LBG-80

Part number: 31765

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	80
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Metals with more than 5% by mass of copper are excluded from use. This excludes printed circuit boards, cables, electrical connectors and coils.
Ambient temperature	-40 °C ... 150 °C
Max. load capacity	6 kN
Product weight	1050 g
Note on materials	RoHS compliant
Mounting material	Spheroidal graphite cast iron
Bolt material	Case-hardened steel
Fuse material	Spring steel