

Right-angle clevis foot LQG-32

Part number: 31768

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	32
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-40 °C ... 150 °C
Max. load capacity	0.9 kN
Product weight	301 g
Product weight	10.61 oz
Note on materials	RoHS compliant
Mounting material	Cast stainless steel
Bolt material	Case-hardened steel
Fuse material	Spring steel