

# Right-angle clevis foot LQG-32

Part number: 31768

FESTO



 [General operating condition](#)

## Data sheet

| Feature                          | Value                    |
|----------------------------------|--------------------------|
| Size                             | 32                       |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| LABS (PWIS) conformity           | VDMA24364-B1/B2-L        |
| Ambient temperature              | -40 °C ... 150 °C        |
| Max. load capacity               | 0.9 kN                   |
| Product weight                   | 301 g                    |
| Product weight                   | 10.61 oz                 |
| Note on materials                | RoHS-compliant           |
| Mounting material                | Cast stainless steel     |
| Bolt material                    | Case-hardened steel      |
| Fuse material                    | Spring steel             |