

# Right-angle clevis foot LQG-63

Part number: 31771

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Size	63
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-40 °C ... 150 °C
Max. load capacity	4 kN
Product weight	784 g
Product weight	27.63 oz
Note on materials	RoHS compliant
Mounting material	Spheroidal graphite cast iron
Bolt material	Case-hardened steel
Fuse material	Spring steel