

# Trunnion support LNZG-40/50

Part number: 32960

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Size	40/50
Based on norm	ISO 15552
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Suitable for battery production with reduced Cu/Zn/Ni values (F1a)
Ambient temperature	-40 °C ... 80 °C
Max. load capacity	2.5 kN
Product weight	129 g
Note on materials	RoHS compliant
Mounting material	Wrought aluminum alloy
Material of bearing	Polymer