

# Non return valve H-1/8-A/I

Part number: 3324

FESTO



 [General operating condition](#)

## Data sheet

| Feature   | Value  |
|---|--|
| Valve function                                    | Non-return function  |
| Pneumatic connection 1                            | G1/8   |
| Pneumatic connection 2                            | G1/8   |
| Type of mounting                                  | Line installation  |
| Normal nominal flow rate (normalized to DIN 1343) | 280 l/min  |
| Operating pressure                                | 0.04 MPa ... 0.8 MPa   |
| Operating pressure                                | 0.4 bar ... 8 bar  |
| Ambient temperature                               | -10 °C ... 60 °C   |
| Housing material                                  | Brass  |
| Operating medium                                  | Compressed air as per ISO 8573-1:2010 [7:-:-]                      |
| Symbol  | 00991455   |
| Information on operating and pilot media          | Operation with oil lubrication possible (required for further use) |
| LABS (PWIS) conformity                            | VDMA24364-B2-L   |
| Temperature of medium                             | -10 °C ... 60 °C   |
| Product weight                                    | 21 g   |
| Seals material                                    | NBR  |