

# Foot mounting DAMH-Q12-6

Part number: 3371840

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Size	6
Mounting position	Any
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	0 °C ... 60 °C
Max. tightening torque	1 Nm
Product weight	27 g
Type of mounting	With through-hole
Note on materials	RoHS compliant
Bracket material	Steel, galvanized