


Foot mounting DAMH-Q12-16

Part number: 3371843

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|----------------------------------|--------------------------|
| Size | 16 |
| Mounting position | Any |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Ambient temperature | 0 °C ... 60 °C |
| Max. tightening torque | 4.9 Nm |
| Product weight | 111 g |
| Type of mounting | With through-hole |
| Note on materials | RoHS-compliant |
| Bracket material | Steel, galvanized |