

# Clevis foot LNG-32

Part number: 33890

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Size	32
Based on norm	ISO 15552 (previously also VDMA 24562, ISO 6431, NF E49 003.1, UNI 10290)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-40 °C ... 80 °C
Max. load capacity	0.9 kN
Product weight	133 g
Note on materials	RoHS-compliant
Mounting material	Tempered steel
Material of bearing	PA