

Solenoid coil MSW-24AC-OD

Part number: 34402

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Actuation type	Electrical
Mounting position	Any
Min. pick-up time	10 ms
Duty cycle	100%
Insulation class	F
Coil characteristics	24 V AC: 50 Hz, initial power 30.0 VA, holding power 22.0 VA
Permissible voltage fluctuations	+/- 10 %
LABS (PWIS) conformity	VDMA24364-C1-L
Storage temperature	-10 °C ... 60 °C
Degree of protection	IP65
Ambient temperature	-5 °C ... 50 °C
Product weight	150 g
Electrical connection	Form A Plug as per EN 175301-803
Type of mounting	External hexagon 1/8 Retaining clip
Note on materials	RoHS-compliant
Solenoid coil material	Duroplast
Material of pin contacts	Brass, tin-plated
Material of winding	Copper