


Guide unit FENG-40-100-KF

Part number: 34500

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	40
Stroke	100 mm
Mounting position	Any
Guide	Recirculating ball bearing
Structural design	Guide
Explosion prevention and protection	Observe the information on the certificate
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-20 °C ... 80 °C
Max. force Fy	1000 N
Max. force Fy static	1260 N
Max. force Fz	1000 N
Max. force Fz static	1260 N
Max. torque Mx	44 Nm
Max. static moment Mx	55 Nm
Max. torque My	52 Nm
Max. static moment My	65 Nm
Max. torque Mz	52 Nm
Max. static moment Mz	65 Nm
Displacement force	15 N
Product weight	2690 g
Type of mounting	With internal thread
Note on materials	RoHS compliant
Material of guide component	Quenched and tempered steel
Housing material	Wrought aluminum alloy, anodized
Material of yoke plate	Wrought aluminum alloy, anodized