

# Quick coupling plug KS3-1/8-A

Part number: 3492

FESTO



 General operating condition

## Data sheet

Feature	Value
Nominal width	4.95 mm
Operating pressure for entire temperature range	-0.095 MPa ... 1.2 MPa
Operating pressure for entire temperature range	-0.95 bar ... 12 bar
Operating pressure for entire temperature range	-13.775 psi ... 174 psi
Normal nominal flow rate (normalized to DIN 1343)	225 l/min ... 648 l/min
Nominal flow rate standardized according to ISO 8778	243.9 l/min ... 702.4 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Lubricated operation possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 60 °C
Nominal tightening torque	5 Nm
Tolerance for nominal tightening torque	±15%
Product weight	13 g
Pneumatic connection 1	External thread G1/8
Note on materials	RoHS compliant
Material of threaded seal	PA66-GF30 / TPE-U
Information on materials	Brass, nickel-plated