

Pneumatic valve VLX-2-3/4-MS-NPT

Part number: 34925

FESTO



[PDF](#) General operating condition

Data sheet

Feature	Value
Structural design	Diaphragm valve
Actuation type	Pneumatic
Sealing principle	Soft
Mounting position	Any
Type of mounting	Line installation
Fitting connection	NPT3/4
Nominal width	20 mm
Valve function	2/2, closed, monostable
Flow direction	Non-reversible
Medium pressure	1 bar ... 10 bar
Exhaust air function	Without flow control option
Reset method	Pneumatic spring
Type of control	Pilot-controlled
Auxiliary pilot air port 12	M5
Pilot medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Symbol	00991371
Medium	Filtered compressed air, 200 µm filter mesh
Temperature of medium	-10 °C ... 80 °C
Ambient temperature	-10 °C ... 60 °C
Normal nominal flow rate (normalized to DIN 1343)	10500 l/min
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Housing material	Brass
Material of screws	High-alloy stainless steel
Material number of screw	1.4301
Product weight	1135 g