


Exhaust protection VABD-D3-SN-N12

Part number: 3535104

FESTO



Data sheet

 [General operating condition](#)

Feature	Value
Mounting position	Any
Symbol	00991455
Operating pressure	0 MPa ... 1.2 MPa
Operating pressure	0 bar ... 12 bar
Explosion prevention and protection	Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Operating medium	Compressed air as per ISO 8573-1:2010 [7::-]
LABS (PWIS) conformity	VDMA24364 zone III
Degree of protection	IP65
Ambient temperature	-50 °C ... 60 °C
Type of mounting	Screw-in With external thread
Note on materials	RoHS-compliant
Seals material	EPDM
Vent screw material	PA