


# Intermediate pressure regulator plate LR-ZP-B-D-3

Part number: 35426

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Based on norm	ISO 5599-1
Structural design	Piston
Integrated function	Pressure regulator
Symbol	00991581
Pressure regulation range MPa	0.05 MPa ... 1.2 MPa
Pressure regulation range	0.5 bar ... 12 bar
Pressure regulation range psi	7.25 psi ... 174 psi
Inlet pressure 1	≤14 bar
Inlet pressure 1 MPa	≤1.4 MPa
Inlet pressure 1 psi	≤203 psi
Certification	UL - Recognized (OL)
LABS (PWIS) conformity	VDMA24364 Zone III
Product weight	1220 g
Note on materials	RoHS compliant
Seals material	NBR
Housing material	Die-cast aluminum Steel