

Low consumption air gun LSP-1/4-D

Part number: 35528

FESTO



[PDF](#) General operating condition

Data sheet

Feature	Value
Exhaust air function	Metered blowing
Symbol	00991454
Operating pressure	0 MPa ... 1 MPa
Operating pressure	0 bar ... 10 bar
Operating pressure	0 psi ... 145 psi
Flow rate with respect to atmosphere	120 l/min
Normal nominal flow rate (normalized to DIN 1343)	120 l/min
Nominal flow rate standardized according to ISO 8778	130 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364 Zone III
Noise level	90 dB(A)
Ambient temperature	-10 °C ... 50 °C
Product weight	240 g
Pneumatic connection	Internal thread G1/4
Note on materials	RoHS compliant
Housing material	Die-cast aluminum, coated