


Vacuum generator VAD-ME-I-3/8

Part number: 35533

FESTO



[General operating condition](#)

Data sheet

Feature	Value
Nominal width of Laval nozzle	2 mm
Mounting position	Any
Ejector characteristics	High vacuum
Integrated function	Ejector pulse valve, electric Electric on-off valve
Structural design	T-shape
Symbol	00991493
Operating pressure	1.5 bar ... 8 bar
Max. vacuum	90 %
Duty cycle	100%
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication not possible
LABS (PWIS) conformity	VDMA24364-B2-L
Temperature of medium	0 °C ... 50 °C
Degree of protection	IP65
Ambient temperature	0 °C ... 50 °C
Electrical connection	Plug
Type of mounting	With internal thread
Pneumatic connection 1	G1/4
Vacuum connection	G3/8
Housing material	Aluminum