

Barb tubing fitting N-1/4-P-9

Part number: 3607

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|---|--|
| Nominal width | 6.5 mm |
| Type of seal on screwed plug | Sealing ring |
| Mounting position | Any |
| Design | Straight design |
| Pack size | 1 |
| Operating pressure for entire temperature range | -0.95 bar ... 16 bar |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:-:-] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -10 °C ... 60 °C |
| Max. tightening torque | 12 Nm |
| Product weight | 7.23 g |
| Pneumatic connection 1 | External thread G1/4 |
| Pneumatic connection 2 | for pneumatic tubing inside diameter 9 mm |
| Note on materials | RoHS-compliant |
| Housing material | Aluminum, anodized |