

Barb tubing fitting N-3/4-P-13

Part number: 3612

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Nominal width	11 mm
Type of seal on screwed plug	Sealing ring
Mounting position	Any
Design	Straight design
Pack size	1
Operating pressure for entire temperature range	-0.95 bar ... 16 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 60 °C
Max. tightening torque	40 Nm
Product weight	32.27 g
Pneumatic connection 1	External thread G3/4
Pneumatic connection 2	for pneumatic tubing inside diameter 13 mm
Note on materials	RoHS compliant
Housing material	Anodized aluminum