

# Coupling piece KSZ-M20X1,5

Part number: 36128

FESTO



 [General operating condition](#)

## Data sheet

| Feature  | Value   |
|--|---|
| Size   | M20x1.5   |
| Mounting position                                  | Any   |
| Threaded connection                                | Internal thread M20x1.5   |
| Corrosion resistance class (CRC)                   | 1 - Low corrosion stress  |
| LABS (PWIS) conformity                             | VDMA24364-B2-L  |
| Suitability for the production of Li-ion batteries | Metals with more than 1% by mass of copper are excluded from use. Circuit boards, lines, electrical push-in connectors and coils are excluded |
| Ambient temperature                                | -40 °C ... 150 °C   |
| Max. load capacity                                 | 9 kN  |
| Product weight                                     | 418 g   |
| Note on materials                                  | RoHS-compliant  |
| Mounting material                                  | Steel<br>Galvanized   |
| Threaded coupling material                         | Steel<br>Galvanized   |