

# Non return valve H-M5

Part number: 3671

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Valve function	Non-return function
Pneumatic connection 1	M5
Pneumatic connection 2	M5
Type of mounting	Line installation
Normal nominal flow rate (normalized to DIN 1343)	115 l/min
Operating pressure	0.04 MPa ... 0.8 MPa
Operating pressure	0.4 bar ... 8 bar
Ambient temperature	-10 °C ... 60 °C
Housing material	Brass
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Symbol	00991455
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
LABS (PWIS) conformity	VDMA24364-B2-L
Temperature of medium	-10 °C ... 60 °C
Note on materials	RoHS-compliant
Seals material	NBR