

Adaptive gripper finger DHAS-GF-60-U-BU

Part number: 3998967

FESTO



Data sheet

 [General operating condition](#)

Feature	Value
Size	60
Mounting position	Any
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Suitability for the production of Li-ion batteries	Suitable for battery production with reduced Cu/Zn/Ni values (F1a)
For use in the food industry	See supplementary material information
Ambient temperature	10 °C ... 50 °C
Product weight	7 g
Note on materials	RoHS-compliant
Clamping jaws material	TPE-U(PU)