

# Position indicator SASF-S2-B-F-A34

Part number: 4046082

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Adjustment range of swivel angle	0 deg ... 90 deg
Dimensions W x L x H	Ø 65 x 40
Vibration resistance	Transport application test with severity level 2 as per FN 942017-4 and EN 60068-2-6
Shock resistance	Shock test with severity level 2 as per FN 942017-5 and EN 60068-2-27
LABS (PWIS) conformity	VDMA24364 Zone III
Ambient temperature	-25 °C ... 70 °C
Product weight	55 g
Type of mounting	As per VDI/VDE 3845
Housing colour	Black
Note on materials	RoHS compliant
Spacer element material	PA
Housing material	PP high-alloy stainless steel
Material of screws	high-alloy stainless steel