

# Position indicator SASF-S2-B-F-A56

Part number: 4077125

FESTO



 [General operating condition](#)

## Data sheet

| Feature                          | Value  |
|----------------------------------|--|
| Adjustment range of swivel angle | 0 deg ... 90 deg   |
| Dimensions W x L x H             | Ø 115 x 62   |
| Vibration resistance             | Transport application test with severity level 2 as per FN 942017-4 and EN 60068-2-6 |
| Shock resistance                 | Shock test with severity level 2 as per FN 942017-5 and EN 60068-2-27                |
| LABS (PWIS) conformity           | VDMA24364 Zone III   |
| Ambient temperature              | -25 °C ... 70 °C   |
| Product weight                   | 140 g  |
| Type of mounting                 | As per VDI/VDE 3845  |
| Housing colour                   | Black  |
| Note on materials                | RoHS compliant   |
| Spacer element material          | PA   |
| Housing material                 | PP<br>high-alloy stainless steel   |
| Material of screws               | high-alloy stainless steel   |