

# Cable fitting NETC-P-M12-EX4

Part number: 4197366

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Ambient temperature	-20 °C ... 70 °C
Degree of protection	IP66 IP68
Type of ignition protection for gas	Ex eb IIC Gb
Type of (ignition) protection for dust	Ex tb IIIC Db
Explosive ambient temperature	-20°C ≤ Ta ≤ +70°C
Explosion protection certification outside the EU	EPL Db (IEC-EX) EPL Gb (IEC-EX)
CE marking (see declaration of conformity)	as per EU explosion protection directive (ATEX) As per EU RoHS directive
Size	M12x1.5
Cable diameter	4 mm ... 7 mm
Color	Blue
Material for cable connector	PA
Seals material	EPDM
Product weight	4 g
Pack size	1
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant
Corrosion resistance class (CRC)	3 - High corrosion stress