

# Cable fitting NETC-P-M12

Part number: 4197367

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Ambient temperature	-20 °C ... 70 °C
Degree of protection	IP68
Note on degree of protection	IP68 at 5 bar for 30 minutes
CE marking (see declaration of conformity)	As per EU RoHS directive
Size	M12x1.5
Cable diameter	3 mm ... 6.5 mm
Color	Black
Material for cable connector	PA
Seals material	EPDM
Product weight	4 g
Pack size	1
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant
Corrosion resistance class (CRC)	3 - High corrosion stress