

# Pressure gauge OH-22-GN

Part number: 4237

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Symbol	00991500
Explosion prevention and protection	Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 45 °C
Product weight	25 g
Pneumatic connection	G1/8
Note on materials	RoHS-compliant