

Moment compensator DARD-L8-40-S

Part number: 4448222

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|---|----------------------------------|
| Size | 32/40 |
| Radial deviation +/- | 2.5 mm |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | 0 °C ... 60 °C |
| Short-term maximum permissible load in direction of force +/- | 3000 N |
| Long-term maximum permissible load in direction of force +/- | 1400 N |
| Product weight | 109 g |
| Note on materials | RoHS compliant Free of copper |
| Adapter material | Anodized aluminum |
| Material of screws | Galvanized steel |