

Ball valve

VZBM-3/8-RP-40-F-3T-F03-B2B3

Part number: 4451854

FESTO



 General operating condition

Data sheet

Feature	Value
Structural design	T hole
Actuation type	Mechanical
Sealing principle	Soft
Mounting position	Any
Type of mounting	In-line installation
Fitting connection	Rp3/8
Switching position indication	Slot direction = flow direction
Flange hole pattern	F03
Inside diameter	10 mm
Nominal width DN	10
Valve function	3/2
Flow direction	Reversible
Nominal pressure of fitting PN	40
Breakaway torque at differential pressure, nominal pressure, fitting PN	6 Nm
Based on norm	ISO 5211
Symbol	00991888
Medium	Compressed air as per ISO 8573-1:2010 [-:--] Inert gas Water – no water vapor Neutral liquids
Temperature of medium	-20 °C ... 130 °C
Flow rate Kv type T corner	9.4 m ³ /h
Note on materials	RoHS compliant
LABS (PWIS) conformity	VDMA24364 Zone III
Housing material	Nickel-plated
Material number of housing	CW617N
Seals material	HNBR PTFE
Ball material	Brass Chrome-plated

Feature	Value
Material number for ball	CW614N
Shaft material	Brass
Material number for shaft	CW614N
Product weight	460 g
CE marking (see declaration of conformity)	as per EU pressure equipment directive
Corrosion resistance class (CRC)	1 - Low corrosion stress