

Ball valve

VZBM-1/4-RP-40-F-3L-F03-B2B3

Part number: 4451869

FESTO



 General operating condition

Data sheet

Feature	Value
Structural design	L bore
Actuation type	Mechanical
Sealing principle	Soft
Mounting position	Any
Type of mounting	In-line installation
Fitting connection	Rp1/4
Switching position indication	Slot direction = flow direction
Flange hole pattern	F03
Inside diameter	8 mm
Nominal width DN	8
Valve function	3/2
Flow direction	Reversible
Nominal pressure of fitting PN	40
Breakaway torque at differential pressure, nominal pressure, fitting PN	6 Nm
Based on norm	ISO 5211
Symbol	00991888
Medium	Compressed air as per ISO 8573-1:2010 [-:--] Inert gas Water – no water vapor Neutral liquids
Temperature of medium	-20 °C ... 130 °C
Flow rate Kv type L	5.9 m ³ /h
Note on materials	RoHS compliant
LABS (PWIS) conformity	VDMA24364 Zone III
Housing material	Nickel-plated
Material number of housing	CW617N
Seals material	HNBR PTFE
Ball material	Brass Chrome-plated

Feature	Value
Material number for ball	CW614N
Shaft material	Brass
Material number for shaft	CW614N
Product weight	530 g
CE marking (see declaration of conformity)	as per EU pressure equipment directive
Corrosion resistance class (CRC)	1 - Low corrosion stress