

Elbow quick connector LCK-3/8-PK-9

Part number: 4474

FESTO



 General operating condition

Data sheet

Feature	Value
Nominal width	8 mm
Type of seal on screwed plug	Sealing ring
Mounting position	Any
Design	L-shape
Pack size	1
Operating pressure for entire temperature range	-0.095 MPa ... 1 MPa
Operating pressure for entire temperature range	-0.95 bar ... 10 bar
Operating pressure for entire temperature range	-13.775 psi ... 145 psi
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Lubricated operation possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 60 °C
Nominal tightening torque	12.5 Nm
Tolerance for nominal tightening torque	±20%
Pneumatic connection 1	External thread G3/8
Pneumatic connection 2	for barbed fitting, inside diameter 9 mm, with nut
Material of union nut	Wrought aluminum alloy, anodized
Note on materials	RoHS compliant
Sealing ring material	PA-reinforced TPE-U(PU)
Hollow bolt material	Wrought aluminum alloy, anodized
Swivel joint material	Die-cast zinc