

# Pneumatic valve VOFC-L-B52-G14-F19A

Part number: 4514928

FESTO



 General operating condition

## Data sheet

Feature	Value
Valve function	5/2-way, bistable
Actuation type	Electrical
Width	40 mm
Normal nominal flow rate (normalized to DIN 1343)	989 l/min
Pneumatic working port	G1/4
Operating pressure	0.25 MPa ... 0.8 MPa
Operating pressure	2.5 bar ... 8 bar
Operating pressure	36.25 psi ... 116 psi
Structural design	Piston gate valve
Degree of protection	IP65
Nominal width	6 mm
Sealing principle	Soft
Mounting position	Any
Manual override	None
Type of control	Piloted
Pilot air supply port	Internal
Flow direction	Non-reversible
Symbol	00991054
Flow rate for piston valve pressurization	1.08 m <sup>3</sup> /h
Flow rate for piston valve exhausting	1.08 m <sup>3</sup> /h
Standard nominal flow rate 2-3	978 l/min
Switching time off	22 ms
On switching time	26 ms
Explosion prevention and protection	Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Operating medium	Compressed air as per ISO 8573-1:2010 [7:2:2]
Corrosion resistance class (CRC)	4 - Particularly high corrosion stress
LABS (PWIS) conformity	VDMA24364 Zone III
Temperature of medium	-25 °C ... 60 °C
Ambient temperature	-25 °C ... 60 °C
Product weight	790 g
Pneumatic connection 1	G1/4
Pneumatic connection 2	G1/4
Pneumatic connection 3	G1/4

<b>Feature</b>	<b>Value</b>
Pneumatic connection 4	G1/4
Pneumatic connection 5	G1/4
Note on materials	RoHS compliant
Seals material	NBR
Housing material	Aluminum, ematal coated