

Pressure gauge OH-22-GE

Part number: 4601

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|--|--|
| Symbol | 00991500 |
| Explosion prevention and protection | Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX) |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:-:-] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -10 °C ... 45 °C |
| Product weight | 25 g |
| Pneumatic connection | G1/8 |
| Note on materials | RoHS compliant |