

Manifold block VABS-S7-RB-B-N14-VDE1-R12

Part number: 4727331

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Mounting position	Any
Pilot air supply port	External Internal
Operating pressure	0 MPa ... 1 MPa
Operating pressure	0 bar ... 10 bar
Explosion prevention and protection	Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Operating medium	Compressed air as per ISO 8573-1:2010 [:-:-]
Corrosion resistance class (CRC)	4 - Particularly high corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Degree of protection	IP65
Type of mounting	With through-hole
Pilot air port 12	1/4 NPT
Pneumatic connection 1	1/4 NPT
Pneumatic connection 2	VDI/VDE 3845 (NAMUR)
Pneumatic connection 3	1/4 NPT
Note on materials	RoHS-compliant
Material of sub-base	Aluminum, ematal coated
Seals material	NBR