

Parallel kit EAMM-U-65-T42-60P-87

Part number: 4784301

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	65
Center-to-center distance	87 mm
Mounting position	Any
Gear ratio	1:1
Max. rotational speed	3000 rpm
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-20 °C ... 60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	0 °C ... 50 °C
Mass moment of inertia	41.2 kgmm ²
No-load driving torque	0.22 Nm
Transferable torque	3 Nm
Product weight	583 g
Interface code, actuator	T42
Interface code, motor in	60P
Note on materials	RoHS-compliant