

Coupling EAMD-21-15-12-8X10

Part number: 4820335

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Diameter of holder 1	12 mm
Diameter of holder 2	8 mm
Size	21
Nominal length	15 mm
Mounting position	Any
Max. rotational speed	10000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 °C ... 60 °C
Mass moment of inertia	0.45 kgmm ²
Transferable torque	2 Nm
Product weight	13.5 g
Note on materials	RoHS-compliant