

Ball valve

VZBE-2-T-63-F-3L-F0507-V15V15

Part number: 4834295

FESTO



 General operating condition

Data sheet

Feature	Value
Structural design	L bore
Actuation type	Mechanical
Sealing principle	Soft
Mounting position	Any
Type of mounting	In-line installation
Fitting connection	2 NPT
Switching position indication	Slot direction = flow direction
Flange hole pattern	F0507
Inside diameter	38.1 mm
Nominal width DN	50
Valve function	3/2
Flow direction	Reversible
Nominal pressure of fitting PN	63
Breakaway torque at differential pressure, nominal pressure, fitting PN	85 Nm
Based on norm	ISO 5211
Symbol	00991888
Medium	Vapor Compressed air as per ISO 8573-1:2010 [-:-:-] Inert gas Water Neutral liquids
Temperature of medium	-20 °C ... 200 °C
Flow rate Kv type L	78 m ³ /h
Note on materials	RoHS compliant
LABS (PWIS) conformity	VDMA24364 Zone III
Housing material	Cast stainless steel
Material number of housing	1,4408
Seat seal material	PTFE
Seals material	PTFE
Ball material	Cast stainless steel

Feature	Value
Material number for ball	1,4408
Shaft material	high-alloy stainless steel
Material number for shaft	1,4401
Product weight	5560 g
Certification	CRN
CE marking (see declaration of conformity)	as per EU pressure equipment directive
Explosion prevention and protection	Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Corrosion resistance class (CRC)	4 - Particularly high corrosion stress