

Drive shaft adapter DARF-Q11-25

Part number: 4835938

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	25
for piston \varnothing	$\varnothing 25$
Structural design	Drive shaft adapter
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 60 °C
Product weight	145 g
Type of mounting	Via through-hole and centering sleeve
Note on materials	RoHS compliant
Material of screws	Steel, nickel-plated