

Drive shaft adapter DARF-Q11-25

Part number: 4835938

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|----------------------------------|---------------------------------------|
| Size | 25 |
| for piston \varnothing | $\varnothing 25$ |
| Structural design | Drive shaft |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -10 °C ... 60 °C |
| Product weight | 145 g |
| Type of mounting | Via through-hole and centering sleeve |
| Note on materials | RoHS-compliant |
| Material of screws | Steel, nickel-plated |