

Drive shaft adapter DARF-Q11-32

Part number: 4835940

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	32
for piston \varnothing	$\varnothing 32$
Structural design	Drive shaft
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 60 °C
Product weight	287 g
Type of mounting	Via through-hole and centering sleeve
Note on materials	RoHS-compliant
Material of screws	Steel, nickel-plated