

Push-on flange DARF-Q12-16

Part number: 4886222

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|----------------------------------|----------------------------------|
| Size | 16 |
| Mounting position | Any |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Ambient temperature | 0 °C ... 60 °C |
| Max. tightening torque | 1.4 Nm |
| Product weight | 25 g |
| Note on materials | RoHS compliant |
| Material of flange | Wrought aluminum alloy, anodized |
| Material of screws | Galvanized steel |