

# Push-on flange DARF-Q12-40

Part number: 4886225

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Size	40
Mounting position	Any
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	0 °C ... 60 °C
Max. tightening torque	5.9 Nm
Product weight	155 g
Note on materials	RoHS-compliant
Material of flange	Wrought aluminum alloy, anodized
Material of screws	Steel, galvanized