

Coupling EAMD-33-22-19-10X12

Part number: 5030024

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Diameter of holder 1	19 mm
Diameter of holder 2	10 mm
Size	33
Nominal length	22 mm
Mounting position	Any
Max. rotational speed	8000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95%
Ambient temperature	-25 °C ... 60 °C
Mass moment of inertia	4.6 kgmm ²
Transferable torque	9 Nm
Product weight	46.1 g
Note on materials	RoHS compliant