

# Coupling EAMD-32-32-9-16X20

Part number: 5038002

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Diameter of holder 1	9 mm
Diameter of holder 2	16 mm
Size	32
Nominal length	32 mm
Mounting position	Any
Max. rotational speed	8000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 °C ... 60 °C
Mass moment of inertia	14.5 kgmm <sup>2</sup>
Transferable torque	12.5 Nm
Product weight	127 g
Note on materials	RoHS-compliant