

# Coupling EAMD-56-46-14-23X27

Part number: 5062229

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Diameter of holder 1	14 mm
Diameter of holder 2	23 mm
Size	56
Nominal length	46.5 mm
Mounting position	Any
Max. rotational speed	5500 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95%
Ambient temperature	-25 °C ... 60 °C
Mass moment of inertia	151 kgmm <sup>2</sup>
Transferable torque	38 Nm
Product weight	424 g
Note on materials	RoHS compliant