


# Linear actuator DLGF-G-32-600-PPSA

Part number: 5074790

FESTO



 General operating condition

## Data sheet

Feature	Value
Stroke	600 mm
Piston diameter	32 mm
Cushioning	Self-adjusting pneumatic end-position cushioning
Mounting position	Any
Guide	Basic guide
Driver principle	Positive locking (slot)
Position sensing	For proximity sensor
Symbol	00995280
Operating pressure	0.15 MPa ... 0.8 MPa
Operating pressure	1.5 bar ... 8 bar
Mode of operation	Double-acting
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Cleanroom suitability, measured according to ISO 14644-14	Class 6 according to ISO 14644-1
Ambient temperature	0 °C ... 60 °C
Cushioning length	11.6 mm
Max. force F <sub>y</sub>	0 N
Max. force F <sub>z</sub> (towards actuator)	276 N
Max. force +F <sub>z</sub> (away from actuator)	138 N
Max. torque M <sub>x</sub>	1.8 Nm
Max. torque M <sub>y</sub>	7.6 Nm
Max. torque M <sub>z</sub>	2.9 Nm
Theoretical force at 6 bar, retracting	483 N
Theoretical force at 6 bar, advancing	483 N
Moving mass	208 g
Product weight	4988 g
Alternative connections	See product drawing
Type of mounting	With accessories
Pneumatic connection	G1/8
Note on materials	RoHS-compliant Copper-free
Cover material	Die-cast aluminum, coated

<b>Feature</b>	<b>Value</b>
Seals material	NBR TPE-U(PU)
Housing material	Aluminum, anodized