

Plug socket with cable SIM-M12-8GD-25-PU

Part number: 5105633

FESTO



 General operating condition

Data sheet

Feature	Value
Conforms to standard	EN 61076-2-101
Cable designation	Without label holder
Electrical connection 1, function	Field device end
Electrical connection 1, design	Round
Electrical connection 1, connection type	Socket
Electrical connection 1, cable outlet	Straight
Electrical connection 1, connection technology	M12x1 A-coded as per EN 61076-2-101
Electrical connection 1, number of pins/wires	8
Electrical connection 1, occupied pins/wires	8
Electrical connection 1, type of mounting	Screw-type lock rotatable
Electrical connection 1, type of mounting	Compatible with rotatable/non-rotatable screw-type lock
Electrical connection for input 1, connection pattern	00992265
Electrical connection 2, function	Control side
Electrical connection 2, connection type	Cable
Electrical connection 2, connection technology	Open end
Electrical connection 2, number of pins/wires	8
Electrical connection 2, occupied pins/wires	8
DC operating voltage range	0 V ... 30 V
Operating voltage range AC	0 V ... 30 V
Current rating at 40° C	2 A
Surge resistance	0.8 kV
Shield	yes
Cable length	25 m
Cable characteristic	Standard
Bending radius, fixed cable installation	≥32 mm
Bending radius, flexible cable installation	≥66 mm
Cable diameter	6.3 mm
Cable diameter tolerance	± 0.2 mm
Cable design	8 x 0.25 mm ²
Nominal conductor cross section	0.25 mm ²
Wire ends	Tin-plated
Degree of protection	IP67
Note on degree of protection	In mounted state
Ambient temperature	-25 °C ... 80 °C
Ambient temperature with flexible cable installation	-5 °C ... 80 °C

Feature	Value
CE marking (see declaration of conformity)	As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant
Contamination level	3
Note on the contamination level	In mounted state
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Material of cable sheath	TPE-U(PUR)
Color cable sheath	Gray
Housing material	TPE-U(PUR)
Material of screw-type lock	Brass, chrome-plated
Seals material	NBR
Material of pin contacts	Copper alloy, gold-plated
Insulating sheath material	PP